



# Standard cylinder CRDSNU-25- -P-A

Part number: 160883

FESTO

Corrosion resistant,  
to DIN ISO 6432, for proximity sensing, with elastic cushioning rings in  
end positions.



Exemplary representation

## Data sheet

Feature	Value
Stroke	10 ... 500 mm
Piston diameter	25 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Conforms to standard	ISO 6432
Design structure	Piston Piston rod
Position detection	For proximity sensor
Working pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Filtered compressed air
Corrosion resistance classification CRC	4
Ambient temperature	-20 ... 80 °C
Authorization	Germanischer Lloyd
Impact energy in end positions	0.3 J
Theoretical force at 6 bar, return stroke	247 N
Theoretical force at 6 bar, advance stroke	295 N
Additional weight per 10 mm stroke	10 g
Basic weight for 0 mm stroke	450 g
Mounting type	with accessories Optional with external (male) thread
Pneumatic connection	G1/8
Materials information for cover	High alloy steel, non-corrosive
Materials information for seals	TPE-U(PU)
Materials information, housing	High alloy steel, non-corrosive
Materials information for piston rod	High alloy steel, non-corrosive