


Standard cylinder DSNU-16- -PPV-A-S10

Part number: 161216

FESTO

Based on DIN ISO 6432, for proximity sensing. Various mounting options, with or without additional mounting components. With adjustable end-position cushioning.

A stroke of at least 10 mm is required for position sensing with proximity sensors.



Exemplary representation

Data sheet

Feature	Value
Stroke	10 ... 200 mm
Piston diameter	16 mm
Piston rod thread	M6
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Conforms to standard	CETOP RP 52 P ISO 6432
Piston-rod end	Male thread
Design structure	Piston Piston rod Cylinder barrel
Position detection	For proximity sensor
Variants	Constant slow movement
Working pressure	1.5 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	5 ... 80 °C
Authorization	Germanischer Lloyd
Impact energy in end positions	0.15 J
Cushioning length	12 mm
Theoretical force at 6 bar, return stroke	103.7 N
Theoretical force at 6 bar, advance stroke	120.6 N
Moving mass with 0 mm stroke	23 g
Additional weight per 10 mm stroke	4.6 g
Basic weight for 0 mm stroke	89.9 g
Additional mass factor per 10 mm of stroke	2 g
Mounting type	with accessories
Pneumatic connection	M5
Materials note	Contains PWIS substances Conforms to RoHS
Materials information for cover	Wrought Aluminum alloy neutral anodization
Materials information for seals	FPM NBR
Materials information for piston rod	High alloy steel, non-corrosive
Materials information for cylinder barrel	High alloy steel, non-corrosive