


# Flow control valve GRO-M5-B

Part number: 151214

FESTO



## Data sheet

Feature	Value
Valve function	Throttle function
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M5
Adjusting element	Knurled screw
Mounting type	Front panel installation with through hole Optional
Standard nominal flow rate in flow control direction	105 l/min
Working pressure	0 ... 10 bar
Ambient temperature	-20 ... 60 °C
Material housing	Wrought Aluminum alloy
Nominal size	2 mm
Assembly position	Any
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-20 ... 60 °C
Product weight	19 g
Materials note	Conforms to RoHS
Material seals	NBR
Material adjusting screw	High alloy steel
Material nut	Wrought Aluminum alloy
Material sleeve	POM