

Flat cylinder DZH-2 1/2"" - -PPV-A

Part number: 16260

FESTO



Data sheet

Feature	Value
Stroke	0,04 in...40 in
Piston diameter	2 1/2 " "
Max. angle of rotation of the piston rod +/-	0.4 deg
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	Any
Mode of operation	Double-acting
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Protection against torsion/guide	Oval piston
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...80 °C
Cushioning length	23 mm
Max. torque for protection against rotation	2 Nm
Theoretical force at 6 bar, retracting	989 N
Theoretical force at 6 bar, advancing	1178 N
Additional weight per 10 mm stroke	80 g
Basic weight with 0 mm stroke	1690 g
Type of mounting	Optionally: With internal thread With accessories
Pneumatic connection	3/8 NPT
Note on materials	RoHS-compliant
Cover material	Aluminum
Seals material	TPE-U(PU)
Housing material	Aluminum
Piston rod material	High-alloy steel