


Servomotor EMMS-AS-55-M-HS-TS-S1

Part number: 1569821

FESTO

Without gear unit.



Data sheet

| Feature | Value |
|--|--|
| Ambient temperature | -10 ... 40 °C |
| Storage temperature | -20 ... 60 °C |
| Relative air humidity | 0 - 90 % |
| Conforms to standard | IEC 60034 |
| Insulation protection class | F |
| Rating class according to EN 60034-1 | S1 |
| Temperature monitoring | PTC resistor |
| Protection class | IP65 |
| Electrical connector system | Plug |
| Materials note | Conforms to RoHS |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| Authorization | RCM Mark c UL us - Recognized (OL) |
| CE symbol (see declaration of conformity) | according to EU-EMV guideline according to EU low voltage guideline |
| Nominal operating voltage DC | 565 V |
| Nominal voltage DC | 565 V |
| Type of winding switch | Star inside |
| Number of pole pairs | 4 |
| Standstill torque | 0.99 Nm |
| Nominal torque | 0.68 Nm |
| Peak torque | 3.8 Nm |
| Nominal rotary speed | 6,600 1/min |
| Max. speed | 7,750 1/min |
| Nominal motor power | 470 W |
| Nominal motor current | 0.8 A |
| Peak current | 4.9 A |
| Motor constant | 0.829 Nm/A |
| Voltage constant, phase-to-phase | 51.54 mVmin |
| Phase-phase winding resistance | 31.3 Ohm |
| Phase-phase winding inductance | 29.3 mH |
| Overall mass moment of inertia at power take-off | 0.223 kgcm ² |
| Product weight | 1,600 g |
| Permissible axial shaft load | 75 N |
| Permissible radial shaft load | 150 N |
| Rotor position sensor | Absolute single turn encoder |
| Rotary position encoder interface | EnDat 22 |
| Rotary position encoder measuring principle | Inductive |
| Rotary position encoder resolution | 18 Bit |
| MTTF, subcomponent | 76 years, rotary position encoder |
| MTTFd, subcomponent | 152 years, rotary position encoder |