


Servomotor EMMS-AS-70-SK-HV-RSB-S1

Part number: 1704793

FESTO

Without gear unit.



Data sheet

| Feature | Value |
|--|--|
| Ambient temperature | -10 ... 40 °C |
| Storage temperature | -20 ... 60 °C |
| Relative air humidity | 0 - 90 % |
| Conforms to standard | IEC 60034 |
| Insulation protection class | F |
| Rating class according to EN 60034-1 | S1 |
| Temperature monitoring | PTC resistor |
| Protection class | IP65 |
| Shaft design Featherkey | DIN 6885 A 4 x 4 x 16 |
| Electrical connector system | Plug |
| Materials note | Conforms to RoHS |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| Authorization | RCM Mark c UL us - Recognized (OL) |
| CE symbol (see declaration of conformity) | according to EU-EMV guideline according to EU low voltage guideline |
| Nominal operating voltage DC | 565 V |
| Nominal voltage DC | 565 V |
| Type of winding switch | Star inside |
| Number of pole pairs | 4 |
| Standstill torque | 1.62 Nm |
| Nominal torque | 1.28 Nm |
| Peak torque | 5.17 Nm |
| Nominal rotary speed | 7,400 1/min |
| Max. speed | 8,200 1/min |
| Nominal motor power | 992 W |
| Nominal motor current | 1.6 A |
| Peak current | 7.5 A |
| Motor constant | 0.798 Nm/A |
| Voltage constant, phase-to-phase | 48.72 mVmin |
| Phase-phase winding resistance | 11.935 Ohm |
| Phase-phase winding inductance | 19.741 mH |
| Overall mass moment of inertia at power take-off | 0.449 kgcm ² |
| Product weight | 2,300 g |
| Permissible axial shaft load | 75 N |
| Permissible radial shaft load | 150 N |
| Rotor position sensor | Absolute single turn encoder |
| Rotary position encoder interface | EnDat 22 |
| Rotary position encoder measuring principle | Inductive |
| Rotor position encoder resolution | 18 Bit |
| Brake holding torque | 2 Nm |
| Operating voltage DC for brake | 24 V |
| Power consumption, brake | 11 W |

| Feature | Value |
|---------------------------------|--|
| Mass moment of inertia of brake | 0.07 kgcm ² |
| Switching cycles, holding brake | 10 million idle actuations (without friction work) |
| MTTF, subcomponent | 76 years, rotary position encoder 1769 years, holding brake |
| MTTFd, subcomponent | 152 years, rotary position encoder |