

Round cylinder DSAA-40- -P

Part number: 172260

FESTO

End cap with air connection in line with cylinder axis
This product is only available if ordered from Festo Korea Co. Ltd.



Exemplary representation



Data sheet

Feature	Value
Stroke	1 ... 500 mm
Piston diameter	40 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Working pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-20 ... 80 °C
Theoretical force at 6 bar, return stroke	633 N
Theoretical force at 6 bar, advance stroke	754 N
Moving mass with 0 mm stroke	469 g
Additional weight per 10 mm stroke	24 g
Basic weight for 0 mm stroke	586 g
Additional mass factor per 10 mm of stroke	15.9 g
Pneumatic connection	G1/4
Materials information for cover	Wrought Aluminum alloy
Materials information for seals	NBR TPE-U(PU)
Materials information, housing	High alloy steel, non-corrosive
Materials information for piston rod	High alloy steel