

# Dual piston rod cylinder DPZ-20-100-P-A-KF-S2

Part number: 162073

FESTO



## Data sheet

| Feature                                  | Value  |
|--|--|
| Stroke                                   | 100 mm   |
| Adjustable end position range/length     | 10 mm  |
| Piston diameter                          | 20 mm  |
| Drive unit operating mode                | Yoke   |
| Cushioning                               | Elastic cushioning rings/pads at both ends                         |
| Mounting position                        | Any  |
| Guide                                    | Recirculating ball bearing guide                                   |
| Structural design                        | Guide  |
| Position sensing                         | For proximity sensor   |
| Variants                                 | Through piston rod   |
| Operating pressure                       | 0.1 MPa...1 MPa<br>1 bar...10 bar                                  |
| Mode of operation                        | Double-acting  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 0 - No corrosion stress  |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Ambient temperature                      | -20 °C...80 °C   |
| Impact energy in the end positions       | 0,2 Nm   |
| Theoretical force at 6 bar, retracting   | 282 N  |
| Theoretical force at 6 bar, advancing    | 282 N  |
| Alternative connections                  | See product drawing  |
| Pneumatic connection                     | M5   |
| Cover material                           | Wrought aluminum alloy   |
| Seals material                           | NBR  |
| Housing material                         | Wrought aluminum alloy   |
| Piston rod material                      | Case-hardened steel  |