

# Flat cylinder DZF-50-25-P-A

Part number: 164068

FESTO



## Data sheet

Feature	Value
Stroke	25 mm
Piston diameter	50 mm Equivalent diameter
Max. angle of rotation of the piston rod +/-	0.5 deg
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Protection against torsion/guide	Oval piston
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Max. torque for protection against rotation	1.2 Nm
Theoretical force at 6 bar, retracting	990 N
Theoretical force at 6 bar, advancing	1178 N
Moving mass at 0 mm stroke	219 g
Additional moving mass per 10 mm stroke	25 g
Additional weight per 10 mm stroke	64 g
Basic weight with 0 mm stroke	854 g
Type of mounting	Optionally: With internal thread With accessories
Pneumatic connection	G1/4
Cover material	Wrought aluminum alloy
Seals material	NBR TPE-U(PU)

Feature	Value
Housing material	Aluminum Smooth anodized
Piston rod material	High-alloy steel