

Swivel/linear unit

DSL-32-40-270-P-S20-CC-KF

Part number: 177238

FESTO

For proximity sensing. Rotary and linear movement can be actuated simultaneously or independently of one another. Rotary movement of 0° - 270° infinitely adjustable.



Data sheet

| Feature | Value |
|--|---|
| Cushioning angle | 12.5 deg |
| Rotation angle adjustment range | 270 deg |
| Stroke | 40 mm |
| Piston diameter | 32 mm |
| Swivel angle | 246 deg |
| Cushioning | CC: Shock absorber at both ends P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Fine adjustment | 1.5 deg |
| Mode of operation | double-acting |
| Design structure | Rotary vane |
| Position detection | For inductive sensors For proximity sensor |
| Variants | S20: through, hollow piston rod |
| Protection against torque/guide | with ball-bearing guide |
| Operating pressure | 2.5 ... 8 bar |
| Max. impact speed | 500 mm/s |
| Max. swivel frequency at 6 bar | 0.7 Hz |
| Operating medium | Dried compressed air, lubricated or unlubricated |
| Ambient temperature | -10 ... 60 °C |
| Cushioning length | 8 mm |
| Torque at 6 bar | 10 Nm |
| Theoretical force at 6 bar, return stroke | 294 N |
| Theoretical force at 6 bar, advance stroke | 403.5 N |
| Permissible mass moment of inertia | 0.00017 kgm ² |
| Additional weight per 10 mm stroke | 109 g |
| Basic weight for 0 mm stroke | 3,280 g |
| Product weight | 3,280 g |
| Mounting type | Clamped in T-slot with external (male) thread Optional |
| Pneumatic connection | G1/8 |
| Materials information for cover | Wrought Aluminum alloy Anodized |
| Materials information for seals | TPE-U(PU) |
| Materials information, housing | Wrought Aluminum alloy Smooth anodized |
| Materials information for piston rod | Heat-treatment steel |