



Ball valve

VZBA-11/2"-GGG-63-32T-F0405-V4V4T

Part number: 1692229

FESTO

3/2-way, flange hole pattern F0405, thread EN 10226-1.



Data sheet

Feature	Value
Design structure	3-way ball valve T hole
Type of actuation	mechanical
Sealing principle	soft
Assembly position	Any
Mounting type	Line installation
Process valve connection	Rp1 1/2
Switching position indicator	Slot direction = flow direction
Flange hole pattern	F04 F05
Inside diameter	31.8 mm
Nominal diameter DN	40
Valve function	3/2
Manual override	None
Flow direction	reversible
Nominal pressure of process valve	63
Actuation torque	42 Nm
Based on the standard	EN 10226-1 ISO 5211
Medium	Compressed air in accordance with ISO8573-1:2010 [-:--] Inert gases Water (no water vapour) Neutral fluids Other media on request
Medium temperature	-10 ... 200 °C
Flow rate Kv, T holes, angular	30 m ³ /h
Flow rate Kv type T straight	62 m ³ /h
Materials note	Conforms to RoHS
PWIS conformity	VDMA24364 zone III
Material housing	High alloy steel, non-corrosive
Material number for housing	1.4408
Material seals	PTFE PTFE reinforced
Material ball	High alloy steel, non-corrosive
Material number for ball	1.4408
Material shaft	High alloy steel, non-corrosive
Material number for shaft	1.4401
Product weight	3,800 g
CE symbol (see declaration of conformity)	according to EU printing device guideline
UKCA marking (see declaration of conformity)	UK regulation for pressure equipment
Corrosion resistance classification CRC	3 - High corrosion stress