


Round cylinder DSAH-10- -P-A

Part number: 171267
Product to be discontinued

FESTO

With bearing cover for direct mounting, end cap with air connection perpendicular to cylinder axis

Type to be discontinued. Available until 2024. See Support Portal for alternative products.



Exemplary representation



Data sheet

Feature	Value
Stroke	1 ... 160 mm
Piston diameter	10 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Working pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-20 ... 80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	39.6 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	47.1 N
Moving mass with 0 mm stroke	11.1 g
Additional mass factor per 10 mm of stroke	1 g
Basic weight for 0 mm stroke	19 g
Additional weight per 10 mm stroke	2.7 g
Pneumatic connection	M4
Material cover	Wrought Aluminum alloy
Material seals	NBR TPE-U(PU)
Material housing	High alloy steel, non-corrosive
Material piston rod	High alloy steel, non-corrosive