


Filter regulator LFR-1/4-D-5M-MINI-A-NPT

Part number: 173769

FESTO



Data sheet

Feature	Value
Size	Mini
Series	D
Mounting position	Vertical
Grade of filtration	5 µm
Condensate drain	Fully automatic
Max. condensate volume	22 cm ³
Bowl guard	Metal bowl guard
Operating pressure	2 bar...12 bar
Max. pressure hysteresis	0.2 bar
Standard nominal flow rate	1200 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gas
Temperature of medium	5 °C...60 °C
Ambient temperature	5 °C...60 °C
Product weight	460 g
Type of mounting	Optionally: Line installation With mounting bracket
Pneumatic connection 1	1/4 NPT
Pneumatic connection 2	1/4 NPT
Note on materials	RoHS-compliant
Housing material	Die-cast zinc
Material of bowl	PC