

# Angled gripper HGWM-08-EO-G7

Part number: 185694

FESTO



## Data sheet

Feature	Value
Size	8
Max. gripper jaw angular play ax, ay	0.5 deg
Max. gripper jaw backlash Sz	0.03 mm
Max. opening angle	17 deg
Pneumatic gripper repetition accuracy	0.02 mm
Number of gripper jaws	2
Actuator system	Pneumatic
Mode of operation	Single-acting Open
Gripper function	Angle
Gripping force backup	Without
Structural design	Inclined plane
Position sensing	None
Operating pressure	2 bar...8 bar
Max. operating frequency of pneumatic gripper	4 Hz
Min. opening time at 6 bar	2.7 ms
Min. closing time at 6 bar	1.2 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	5 °C...60 °C
Spring return torque	0,5 Ncm
Total gripping torque at 6 bar, closing	22 Ncm
Maximum force on gripper jaw Fz, static	7 N
Maximum torque on gripper jaw, Mx static	20 Ncm
Maximum torque on gripper jaw, My static	20 Ncm
Maximum torque on gripper jaw, Mz static	20 Ncm
Product weight	14 g
Type of mounting	With lock nut
Pneumatic connection	M3
Note on materials	RoHS-compliant
Cover cap material	POM

Feature	Value
Housing material	High-alloy stainless steel
Gripper jaw material	High-alloy steel