

Semi-rotary actuator DRE-50-F10-Q12-FO-C

Part number: 190214

FESTO

Single-acting, air connection as per VDI/VDE 3845, Namur valves can be directly flange-mounted



Data sheet

Feature	Value
Size of actuator	50
Flange hole pattern	F10
Swivel angle	90 deg
Fitting connection conforms to standard	ISO 5211
Cushioning	No cushioning
Assembly position	Any
Mode of operation	single-acting
Design structure	Rack and pinion
Position detection	No
Closing direction	Spring force, opening
Valve connection conforms to standard	VDI/VDE 3845 (NAMUR)
Working pressure	2 ... 10 bar
ATEX category Gas	II 2G
Explosion ignition protection type Gas	c T6
ATEX category Dust	II 2D
Explosion ignition protection type Dust	c 60°C
Explosion-proof ambient temperature	-20°C ≤ Ta ≤ +60°C
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
CE symbol (see declaration of conformity)	according to EU-Ex protection guideline (ATEX)
Corrosion resistance classification CRC	4
Ambient temperature	-20 ... 80 °C
Air consumption at 6 bar per cycle 0°-90°-0°	12 l
Product weight	12,200 g
Shaft connection	V22
Pneumatic connection	Subbase G1/4
Materials note	Contains PWIS substances