


# Tandem cylinder DNCT-4<sup>\*\*\*</sup> - -PPV-A-S6

Part number: 191222

FESTO



## Data sheet

| Feature                                  | Value   |
|--|---|
| Stroke                                   | 3 mm...500 mm   |
| Based on norm                            | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Cushioning                               | Pneumatic cushioning, adjustable at both ends                             |
| Mode of operation                        | Double-acting   |
| Operating pressure                       | 0.06 MPa...1 MPa<br>0.6 bar...10 bar                                      |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                             |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use)        |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress   |
| LABS (PWIS) conformity                   | VDMA24364-B2-L  |
| Cushioning length                        | 32 mm   |
| Pneumatic connection                     | 1/2 NPT   |
| Note on materials                        | RoHS-compliant  |
| Cover material                           | Die-cast aluminum   |
| Seals material                           | FPM   |
| Housing material                         | Wrought aluminum alloy  |
| Piston rod material                      | High-alloy steel  |