

# Air line lubricator LOE-1/2-D-MAXI

Part number: 186480

FESTO



## Data sheet

Feature	Value
Size	Maxi
Series	D
Mounting position	Vertical +/- 5°
Structural design	Proportional standard oil mist lubricator
Max. oil capacity	190 cm <sup>3</sup>
Bowl guard	Metal bowl guard
Operating pressure	0 bar...16 bar
Minimum flow rate for lubricator function	10 l/min
Standard nominal flow rate	8300 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:4:-] Inert gas
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	1100 g
Type of mounting	With accessories
Pneumatic connection 1	G1/2
Pneumatic connection 2	G1/2
Note on materials	RoHS-compliant
Material of bowl	PC