


Ball valve actuator unit VZBA-1/4^{''}-GGG-63-32T-F0304-V4V4T-PS30-R-90-4-C

FESTO

Part number: 1915744



Data sheet

| Feature | Value |
|--|--|
| Structural design | 3-way ball valve Drilled T hole |
| Actuation type | Pneumatic |
| Mounting position | Any |
| Type of mounting | Line installation |
| Fitting connection | Rp1/4 |
| Switching position indication | Slot direction = flow direction |
| Nominal width DN | 8 |
| Operating pressure | 6 bar...8.4 bar |
| Nominal pressure of fitting PN | 63 |
| Medium | Compressed air as per ISO 8573-1:2010 [:-:-] Inert gas Water – no water vapor Neutral liquids |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Temperature of medium | -10 °C...200 °C |
| Ambient temperature | -10 °C...80 °C |
| Flow rate Kv type T corner | 4.5 m ³ /h |
| Flow rate Kv type T straight | 8 m ³ /h |
| Max. surface temperature of assembly | TX |
| Explosion group of assembly | IIC, IIIC |
| Note on materials | RoHS-compliant |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Housing material | High-alloy stainless steel |
| Material number of housing | 1.4408 |
| Seals material | PTFE PTFE-reinforced |
| Ball material | High-alloy stainless steel |
| Material number for ball | 1.4408 |
| Shaft material | High-alloy stainless steel |
| Material number for shaft | 1.4401 |
| Product weight | 2950 g |

| Feature | Value |
|-------------------------------------|--|
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Explosive ambient temperature | -10°C ≤ Ta ≤ +60°C |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |