


Controls FEC-FC34-FST

Part number: 190587

FESTO

FEC compact, 12 inputs / 2 relays, 6 transistor outputs, 24 V DC, Ethernet 10BaseT, FST, for the network, in plastic housing, with threaded connection, 2 serial interfaces.

Run-out type. Available until 2010.



Data sheet

Feature	Value
Authorization	C-Tick
Operating voltage	24 VDC +25% / -15%
Current consumption	180 mA nominal at 24 V DC
Power supply cable length	10 m
Ambient temperature	0 ... 55 °C
Storage temperature	-25 ... 70 °C
Relative air humidity	95% non-condensing
Protection class	IP20
Safety class	III
Product weight	160 g
Test for insensitivity to vibration	EN 60068-2-6-FC 10-57 Hz 0,075 mm 57 - 150 Hz 1g
Test for insensitivity to shock	EN 60068-2-27 EA 15g, 11ms 2 shocks per direction
Run/Stop switch	Yes
Electrical connector technology, I/O	Screw connector
Status displays	LED
Digital inputs, number	12
Digital inputs, fast counting inputs	2, each with max. 2 kHz
Digital inputs, incremental encoder connection	Yes, max. 200 Hz
Digital inputs, input signal delay	5 ms typ.
Digital inputs, input voltage/current	24 VDC / 7 mA
Digital inputs, nominal value for True	≥ 15 VDC
Digital inputs, nominal value for False	≤ 5 VDC
Digital inputs, electrical isolation	Yes, via optocoupler
Digital inputs, status display	LED
Digital inputs, permissible connector cable length	30 m
Digital outputs, number	8
Digital outputs, contact	6 transistors, 2 relays
Digital outputs, output voltage	Transistor: 24 V DC / relay: 30 V DC, 250 V AC
Digital outputs, output current	Transistor: 600 mA / relay: 5 A
Digital outputs, group current	3.2 A
Digital outputs, electrical isolation	Yes
Digital outputs, electrical isolation in groups	Yes, in groups of up to 4 or 2
Digital outputs, switching frequency	Transistor: max. 1 kHz, relay: 25 Hz
Digital outputs, switching cycles	Relay: 100,000
Digital outputs, short circuit proof	Transistor: yes
Digital outputs, overload proof	Transistor: yes
Digital outputs, resistant to low-resistance loads	Transistor: yes, up to 5 W

Feature	Value
Digital outputs, status display	LED
Serial interface, number	2
Serial interface, COM / EXT attributes	TTL level, no electrical isolation
Serial interface, connection technology	2x RJ12 socket
Serial interface, used as RS 232C	SM14 or SM15 required
Serial interface, used as universal interface: EXT	300...115000 Bd 7N1, 7E1, 7O1, 8N1, 8E1, 8O1
Ethernet, connector plug	RJ45
Ethernet, number	1
Ethernet, bus interface	IEEE802.3 (10Base T)
Ethernet, data transmission speed	10 Mbit/s
Ethernet, supported protocols	TCP/IP, EasyIP, http
Programming, language	AWL, KOP
Programming, operating language	DE, EN
Programming, number of programs and tasks per project	64
Programming, number of registers (words)	256
Programming, number of markers	10000
Programming, number of timers (status, actual value, set point)	256
Programming, number of counters (status, actual value, set point)	256
Programming, support for C/C++	Yes
Programming, file handling support	Yes
CE symbol (see declaration of conformity)	according to EU-EMV guideline