


Air solenoid valve MFH-5/3G-3/8-B

Part number: 19707

FESTO



Data sheet

| Feature | Value |
|--|--|
| Valve function | 5/3, closed |
| Actuation type | Electrical |
| Width | 40 mm |
| Standard nominal flow rate | 2200 l/min |
| Pneumatic working port | G3/8 |
| Operating pressure | 0.3 MPa...1 MPa 3 bar...10 bar |
| Structural design | Piston gate valve |
| Reset method | Mechanical spring |
| Nominal width | 12 mm |
| Width dimension | 41 mm |
| Exhaust air function | With flow control option |
| Sealing principle | Soft |
| Mounting position | Any |
| Manual override | Non-detenting |
| Type of control | Pilot-controlled |
| Pilot air supply port | Internal |
| Flow direction | Non-reversible |
| Lap | Overlap |
| Max. switching frequency | 3 Hz |
| Switching time off | 80 ms |
| On switching time | 24 ms |
| Max. positive test pulse with 0 signal | 2200 µs |
| Max. negative test pulse on 1 signal | 3700 µs |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -40 °C...60 °C |
| Temperature of medium | -10 °C...60 °C |
| Ambient temperature | -5 °C...40 °C |
| Product weight | 780 g |

| Feature | Value |
|---------------------------|--|
| Electrical connection | Via F coil, to be ordered separately |
| Type of mounting | Optionally: On PR rail With through-hole |
| Pilot exhaust air port 82 | M5 |
| Pilot exhaust air port 84 | M5 |
| Pneumatic connection 1 | G3/8 |
| Pneumatic connection 2 | G3/8 |
| Pneumatic connection 3 | G3/8 |
| Pneumatic connection 4 | G3/8 |
| Pneumatic connection 5 | G3/8 |
| Note on materials | RoHS-compliant |
| Seals material | NBR |
| Housing material | Die-cast aluminum |