

Trunnion support LNZG-32

Part number: 32959

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | 32 |
| Based on norm | ISO 15552 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils |
| Ambient temperature | -40 °C...80 °C |
| Product weight | 83 g |
| Note on materials | RoHS-compliant |
| Mounting material | Wrought aluminum alloy |
| Material of bearing | Polymer |