

Quick coupling EAMD-42-40-14-16X25-U

Part number: 3420022

FESTO



Data sheet

| Feature | Value |
|------------------------|----------------------|
| Diameter of holder 1 | 14 mm |
| Diameter of holder 2 | 16 mm |
| Size | 42 |
| Nominal length | 40 mm |
| Mounting position | Any |
| Max. rotational speed | 6000 1/min |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C...60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -25 °C...60 °C |
| Mass moment of inertia | 39 kgmm ² |
| Transferable torque | 21 Nm |
| Product weight | 196 g |
| Note on materials | RoHS-compliant |