

Controller CPX-E-CEC-C1-EP

Part number: 4252742

FESTO



Data sheet

| Feature | Value |
|--|---|
| Width dimension | 18.9 mm |
| Type of mounting | With H-rail |
| Product weight | 288 g |
| Mounting position | Vertical Horizontal |
| Ambient temperature | -5 °C...50 °C |
| Note on ambient temperature | -5 - 60 °C for vertical installation |
| Storage temperature | -20 °C...70 °C |
| Relative air humidity | 95 % Non-condensing |
| Degree of protection | IP20 |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| Protection against direct and indirect contact | PELV |
| LABS (PWIS) conformity | VDMA24364 zone III |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU RoHS directive |
| Certification | RCM compliance mark c UL us - Listed (OL) |
| Note on materials | RoHS-compliant |
| Diagnostics via LED | Module status Network status Network status, engineering port 1 Engineering port 2 network status EtherCAT network status Network status, port 1 Network status, port 2 Run Power supply for electronics/sensors Load power supply System fault |
| Control elements | DIL switch for RUN/STOP Rotary switch for address setting Optional: CDSB operating unit |

| Feature | Value |
|--|---|
| Fieldbus interface, protocol | ACD (Address Conflict Detection) DLR (Device Level Ring) EtherNet/IP EtherNet/IP QoS EtherNet/IP Quickconnect SNMP |
| Fieldbus interface, connection type | 2x socket |
| Fieldbus interface, connection technology | RJ45 |
| Fieldbus interface, number of poles/wires | 8 |
| Fieldbus interface 2, type | Ethernet |
| Fieldbus interface 2, protocol | CoE EoE EtherCAT® FoE |
| Fieldbus interface 2, function | Bus connection, forwarding |
| Fieldbus interface 2, connection type | Socket |
| Fieldbus interface 2, connection technology | RJ45 |
| Fieldbus interface 2, number of poles/wires | 8 |
| Fieldbus interface 2, galvanic isolation | yes |
| Fieldbus interface 2, transmission rate | 100 Mbit/s |
| Ethernet interface, connection type | 2x socket |
| Ethernet interface, protocol | EasyIP Modbus® TCP OPC-UA TCP/IP |
| Ethernet interface, function | Diagnostics Switch |
| Ethernet interface, connection technology | RJ45 |
| Ethernet interface, number of poles/wires | 8 |
| Ethernet interface, transmission rate | 10 Mbit/s 100 Mbit/s |
| Max. address capacity inputs | 64 byte |
| Fieldbus interface, max. address volume for inputs | 512 byte |
| Max. address capacity outputs | 64 byte |
| Fieldbus interface, max. address volume for outputs | 512 byte |
| System parameter | Diagnostic memory Fail-safe response System start |
| Module parameters | Channel alarm bundling Undervoltage diagnostics Channel alarms for undervoltage Analog module process value representation |
| Configuration support | Operator unit CDSB CODESYS V3 |
| Additional functions | CODESYS V3 |
| Power supply, function | Electronics and sensors |
| Power supply, type of connection | Terminal strip |
| Power supply, note on connection type | > 4 A and UL 2x terminal strip for power supply |
| Power supply, connection technology | Spring-loaded terminal |
| Power supply, number of pins/wires | 4 |
| Nominal operating voltage DC for electronics/sensors | 24 V |
| Permissible voltage fluctuations for electronics/sensors | ± 25 % |
| Power supply, conductor diameter | 0.2 mm ² ...1.5 mm ² |
| Power supply, information on conductor diameter | 0.2 - 2.5 mm ² for flexible conductors without cable end sleeves |
| Intrinsic current consumption at nominal operating voltage for electronics/sensors | Typically 150 mA |
| Power failure buffering | 20 ms |
| Reverse polarity protection | 24 V sensor supply against 0 V sensor supply |

| Feature | Value |
|----------------------|--|
| Programming software | CODESYS provided by Festo |
| Program memory | 100 MB user program |
| Processing time | Approx. 200 µs/1 k instruction |
| Flag | 120 kB remanent data CODESYS variable concept |