

Ball valve VZBD-1/2-S5-16-T-2-F0304-V14V14

Part number: 4802244

FESTO



Data sheet

| Feature | Value |
|--------------------|---------------------------------|
| Structural design | 2-way ball valve |
| Actuation type | Mechanical |
| Sealing principle | Soft |
| Mounting position | Any |
| Type of mounting | Line installation |
| Fitting connection | Clamp as per DIN 32676 series A |

| Feature | Value |
|---|--|
| Switching position indication | Slot direction = flow direction |
| Flange hole pattern | F0304 |
| Inside diameter | 18.1 mm |
| Nominal width DN | 15 |
| Valve function | 2/2 |
| Flow direction | Reversible |
| Nominal pressure of fitting PN | 16 |
| Breakaway torque at differential pressure, nominal pressure, fitting PN | 7 Nm |
| Based on norm | DIN 32676 ISO 5211 |
| Medium | Vapor Compressed air as per ISO 8573-1:2010 [:-:-] Inert gas Water Neutral liquids |
| Temperature of medium | -20 °C...200 °C |
| Flow rate Kv | 46 m ³ /h |
| Note on materials | RoHS-compliant |
| LABS (PWIS) conformity | VDMA24364 zone III |
| For use in the food industry | See supplementary material information |
| Housing material | Cast stainless steel |
| Material number of housing | 1.4409 |
| Seat seal material | PTFE, modified |
| Seals material | FPM PTFE |
| Ball material | Cast stainless steel |
| Material number for ball | 1.4409 |
| Shaft material | High-alloy stainless steel |
| Material number for shaft | 1.4401 |
| Product weight | 830 g |
| Certification | 3-A sanitary CRN |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Corrosion resistance class (CRC) | 4 - Particularly high corrosion stress |