


Parallel gripper HGPL-14-60-A-B

Part number: 3361481

FESTO



Data sheet

Feature	Value
Size	14
Stroke per gripper jaw	60 mm
Max. interchangeability	0.2 mm
Max. gripper jaw angular play ax, ay	0.2 deg
Max. gripper jaw backlash Sz	0.05 mm
Rotational symmetry	0.2 mm
Pneumatic gripper repetition accuracy	0.03 mm
Number of gripper jaws	2
Actuator system	Pneumatic
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Parallel
Gripping force backup	Without
Structural design	Twin piston Guide Piston gate valve T-shape Gear rack/pinion
Position sensing	For proximity sensor
Gripping force per gripper jaw at 6 bar, opening	126 N 63 N
Gripping force per gripper jaw at 6 bar, closing	158 N 79 N
Operating pressure	3 bar...8 bar
Max. operating frequency of pneumatic gripper	1 Hz
Min. opening time at 6 bar	270 ms
Min. closing time at 6 bar	230 ms
Max. mass per external gripper finger	80 g
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	5 °C...60 °C

Feature	Value
Mass moment of inertia	11.43 kgcm ²
Maximum force on gripper jaw Fz, static	500 N
Maximum torque on gripper jaw, Mx static	35 Nm
Maximum torque on gripper jaw, My static	35 Nm
Maximum torque on gripper jaw, Mz static	35 Nm
Relubrication interval for guidance elements	5 MioCyc
Product weight	595 g
Type of mounting	With internal thread and centering sleeve Via through-hole and centering sleeve
Pneumatic connection	M5
Note on materials	RoHS-compliant
Housing material	Wrought aluminum alloy, smooth-anodized
Gripper jaw material	Hardened steel