

Round cylinder DSNU-S-8-10-P-A-MQ

Part number: 5205897

FESTO



Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	8 mm
Piston rod thread	M4
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Structural design	Piston Piston rod Cylinder barrel
Position sensing	For proximity sensor
Operating pressure	0.15 MPa...1 MPa 1.5 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-20 °C...80 °C
Theoretical force at 6 bar, retracting	22.6 N
Theoretical force at 6 bar, advancing	30.2 N
Moving mass at 0 mm stroke	6.3 g
Additional moving mass per 10 mm stroke	1 g
Basic weight with 0 mm stroke	20 g
Additional weight per 10 mm stroke	2.4 g
Type of mounting	With accessories
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy, anodized
Seals material	TPE-U(PU)
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	High-alloy stainless steel