

# Pressure gauge kit DPA-100-10-MA-SET

Part number: 526098

FESTO



## Data sheet

| Feature                     | Value                       |
|-----------------------------|-----------------------------|
| Conforms to standard        | EN 837-1                    |
| Pressure gauge nominal size | 40                          |
| Structural design           | Bourdon tube pressure gauge |
| Type of mounting            | With external thread        |
| Operating pressure          | 10 bar                      |
| Measurement accuracy class  | 2.5                         |
| Degree of protection        | IP43                        |
| Ambient temperature         | 5 °C...60 °C                |
| LABS (PWIS) conformity      | VDMA24364-B1/B2-L           |
| Mounting position           | Any                         |
| Pneumatic connection        | G1/4                        |
| Product weight              | 305 g                       |