


Feed separator HPV-22-60-A

Part number: 529354

FESTO



Data sheet

Feature	Value
Stroke	60 mm
Piston diameter	22 mm
Max. interchangeability	0.3 mm
Max. tappet play Sx	0.05 mm
Max. tappet play Sz	0.03 mm
Max. gripper jaw angular backlash	0.04 deg
Max. gripper jaw angular backlash ay	0.07 deg
Max. gripper jaw angular backlash az	0.12 deg
External finger mounting	Through-hole
Cushioning	No cushioning
Mounting position	Any
Mode of operation	Double-acting
Structural design	Twin piston Piston rod Stop valve Anti-twist feature
Position sensing	For proximity sensor
Half pulse	398.1 ms
Protection against torsion/guide	Square guide
Cycle time	796.1 ms
Operating pressure	3 bar...8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	5 °C...60 °C
Max. force on finger Fz static	180 N
Max. static moment Mr at finger	9 Nm
Max. static moment Mx at finger	9 Nm
Max. static moment at finger	9 Nm
Theoretical force at 6 bar, retracting	180 N
Theoretical force at 6 bar, advancing	225 N

Feature	Value
Product weight	1500 g
Max. mass per external gripper finger	395 g
Alternative connections	M5
Type of mounting	Optionally: With internal thread and centering sleeve Via through-hole and centering sleeve
Pneumatic connection	M5