



Vacuum generator

VN-14-L-T4-PI5-VI5-RO2-A

Part number: 532720

FESTO

With ejector pulse. Standard, high suction rate, width 18 mm, T shape with female thread and open silencer.



Data sheet

| Feature | Value |
|--|--|
| Nominal size, Laval nozzle | 1.4 mm |
| Grid dimension | 18 mm |
| Design, silencer | open |
| Assembly position | Any |
| Ejector characteristic | Standard High suction volume |
| Integrated function | Ejector pulse valve, pneumatic Open silencer |
| Design structure | T-shaped |
| Working pressure for max. suction rate | 5 bar |
| Working pressure | 1 ... 8 bar |
| Nominal working pressure | 6 bar |
| Max. suction rate with respect to atmosphere | 92.6 l/min |
| Air supply time at nominal working pressure | 0.28 s |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation not possible |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364 zone III |
| Medium temperature | 0 ... 60 °C |
| Recommendation for cleaning | Soap suds |
| Noise level at nominal operating pressure | 69 dB(A) |
| Ambient temperature | 0 ... 60 °C |
| Max. tightening torque | 0.5 Nm |
| Product weight | 94 g |
| Mounting type | with through hole with top-hat rail with accessories |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 3 | Open silencer |
| Vacuum connection | G1/4 |
| Material of connecting thread | Wrought aluminum alloy, anodized |
| Materials note | Conforms to RoHS |
| Material seals | NBR |
| Material receiver nozzle | POM |
| Material housing | PA-reinforced POM-reinforced |
| Material silencer | Wrought Aluminum alloy POM PU foam |
| Material screws | Steel |
| Material transmitter nozzle | Wrought Aluminum alloy |