

Motor cable NEBM-H6G4-K-2.5-Q13N-LE4

Part number: 5219193

FESTO



Data sheet

Feature	Value
Cable designation	Without label holder
Electrical connection 1, function	Field device end
Electrical connection 1, design	Rectangular
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	Connection diagram H6, coded for motor
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
DC operating voltage range	0 V...300 V
Operating voltage range AC	0 V...300 V
Current rating at 40° C	9.5 A
Surge resistance	2 kV
Cable length	2.5 m
Cable characteristic	Standard
Connector cable test conditions	Test conditions on request
Bending radius, fixed cable installation	74 mm
Bending radius, flexible cable installation	111 mm
Cable diameter	7.4 mm
Cable design	4 x 0.79 mm ²
Nominal conductor cross section	0.79 mm ² AWG18
Wire ends	Cable end sleeve
Degree of protection	IP20
Note on degree of protection	In mounted state
Ambient temperature	-25 °C...90 °C
Ambient temperature with flexible cable installation	-25 °C...90 °C

Feature	Value
CE marking (see declaration of conformity)	As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK instructions for electrical equipment
LABS (PWIS) conformity	VDMA24364 zone III
Note on materials	RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	0 - No corrosion stress
Material of cable sheath	TPE-E
Color cable sheath	Black
Housing material	PA
Housing colour	White
Insulating sheath material	TPE-E