

Ball valve VAPB-1 1/4-F-40-F0405

Part number: 534307

FESTO



Data sheet

Feature	Value
Structural design	2-way ball valve
Actuation type	Mechanical
Sealing principle	Soft
Mounting position	Any
Type of mounting	Line installation
Fitting connection	Rp1 1/4

Feature	Value
Switching position indication	Slot direction = flow direction
Flange hole pattern	F04 F05
Nominal width DN	32
Flow direction	Reversible
Nominal pressure of fitting PN	40
Breakaway torque at differential pressure, nominal pressure, fitting PN	15 Nm
Breakaway torque at 10 bar differential pressure	11.9 Nm
Based on norm	ISO 5211
Medium	Compressed air as per ISO 8573-1:2010 [:-:-] Inert gas Water Neutral liquids
Temperature of medium	-20 °C...150 °C
Flow rate Kv	121 m³/h
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Housing material	Brass Nickel-plated
Material number of housing	2.0402 CW617N
Seals material	HNBR PTFE
Ball material	Brass Hard-chrome-plated
Material number for ball	2.0402 CW617N
Shaft material	Brass
Material number for shaft	2.0401 CW614N
Product weight	1300 g
Corrosion resistance class (CRC)	1 - Low corrosion stress