


Ball valve

VAPB-4-F-63-F10-CR

Part number: 534321

FESTO

Corrosion and acid resistant



Data sheet

Feature	Value
Design structure	2-way ball valve
Type of actuation	mechanical
Sealing principle	soft
Mounting type	Line installation
Process valve connection	Rp4
Flange hole pattern	F10
Inside diameter	100 mm
Nominal diameter DN	100
Nominal pressure of process valve	63
Actuation torque	95 Nm
Operating medium	Compressed air in accordance with ISO8573-1:2010 [-:--:] Inert gases Water Neutral fluids
Medium temperature	-10 ... 180 °C
Flow rate Kv	1,414 m ³ /h
Materials information, housing	High alloy steel, non-corrosive
Material number for housing	1.4408
Materials information for seals	FPM PTFE
Material information, globe	High alloy steel, non-corrosive
Material number for ball	1.4401
Materials information for shaft	High alloy steel, non-corrosive
Material number for shaft	1.4401
Product weight	22,300 g
CE symbol (see declaration of conformity)	according to EU printing device guideline
Corrosion resistance classification CRC	3