

Active carbon filter MS12-LFX

Part number: 535043

FESTO



Data sheet

Feature	Value
Size	12
Series	MS
Mounting position	Vertical +/- 5°
Structural design	Active carbon filter
Operating pressure	0 bar...20 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [1:4:2] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [1:4:1]
Temperature of medium	5 °C...30 °C
Residual oil content	0.003 mg/m ³
Ambient temperature	-10 °C...60 °C
Type of mounting	Optionally: Line installation With accessories
Note on materials	RoHS-compliant
Compressed air filter material	Activated carbon
Housing material	Die-cast aluminum
Material of bowl	Wrought aluminum alloy