



# Proximity sensor SIED-M18NB-ZS-K-L-PA

Part number: 538337

FESTO



## Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive
Measuring principle	Inductive
Rated operating distance	8 mm
Assured operating distance	6.48 mm
Reduction factors	Aluminum = 0.35 - 0.5 Stainless steel St 18/8 = 0.6 - 1.0 Copper = 0.25 - 0.45 Brass = 0.35 - 0.5 Steel St 37 = 1.0
Ambient temperature	-25 °C...70 °C
Repetition accuracy	0.16 mm
Switching output	Non-contact, 2-wire
Switching element function	N/O contact
Hysteresis	0.24 mm...1.2 mm
Max. switching frequency DC	60 Hz
Max. switching frequency AC	20 Hz
Max. output current	300 mA
Voltage drop	6 V
Minimum load current	3 mA
Short-circuit protection	no
Operating voltage range AC	20 V...250 V
DC operating voltage range	10 V...300 V
Mains frequency	50 Hz...60 Hz
Idle current	1.5 mA
Reverse polarity protection	for all electrical connections
Electrical connection	2-wire Cable
Cable length	2.5 m

<b>Feature</b>	<b>Value</b>
Material of cable sheath	PVC
Insulating sheath material	PVC
Size	M18
Type of mounting	With lock nut
Tightening torque	2 Nm
Mounting type	Not flush
Product weight	123 g
Housing material	PA-reinforced
Switching status indication	LED yellow
Ambient temperature with flexible cable installation	0 °C...70 °C
Degree of protection	IP65 IP67
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
Selection of additional sensor information	For direct and alternating voltage
Electrical output	Non-contact, 2-wire
Selection of sensor version	Polyamide housing