

Filter regulator MS12N-LFR

Part number: 535025

FESTO



Data sheet

Feature	Value
Size	12
Series	MS
Actuator lock	Rotary knob with detent Rotary knob with integrated lock can be closed with accessories
Mounting position	Vertical +/- 5°
Structural design	Filter regulator with pressure gauge
Pressure gauge	with pressure gauge
Max. pressure hysteresis	0.4 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [-:4:-] Compressed air as per ISO 8573-1:2010 [7:4:-] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-10 °C...60 °C
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Type of mounting	Optionally: Line installation With accessories
Housing material	Die-cast aluminum
Material of bowl	Wrought aluminum alloy