

Mini slide DGSL-6-30-PA

Part number: 543918

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 30 mm |
| Adjustable end-position range/front length | 30.5 mm |
| Adjustable end-position range/rear length | 15 mm |
| Piston diameter | 8 mm |
| Drive unit operating mode | Yoke |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Guide | Ball bearing cage guide |
| Structural design | Yoke Piston Piston rod Slide |
| Position sensing | For proximity sensor |
| Operating pressure | 0.15 MPa...0.8 MPa 1.5 bar...8 bar |
| Max. speed | 0.5 m/s |
| Repetition accuracy | 0.3 mm |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 °C...60 °C |
| Impact energy in the end positions | 0,05 Nm |
| Cushioning length | 1.5 mm |
| Max. force F _y | 631 N |
| Max. force F _z | 631 N |
| Max. torque M _x | 8 Nm |
| Max. torque M _y | 5.5 Nm |
| Max. torque M _z | 5.5 Nm |
| Theoretical force at 6 bar, retracting | 23 N |
| Theoretical force at 6 bar, advancing | 30 N |

| Feature | Value |
|-------------------------|----------------------------|
| Moving mass | 83 g |
| Product weight | 204 g |
| Alternative connections | See product drawing |
| Type of mounting | With through-hole |
| Pneumatic connection | M3 |
| Note on materials | RoHS-compliant |
| Cover material | Wrought aluminum alloy |
| Seals material | HNBR |
| Housing material | Wrought aluminum alloy |
| Piston rod material | High-alloy stainless steel |