


Air solenoid valve VZWM-L-M22C-G112-F5

Part number: 546152

FESTO



Data sheet

Feature	Value
Structural design	Diaphragm valve servo-controlled
Actuation type	Electrical
Sealing principle	Soft
Mounting position	Preferably upright
Type of mounting	Line installation
Fitting connection	G1 1/2
Electrical connection	Solenoid coil type MH-... , coil can be ordered as an accessory
Nominal width	40 mm
Valve function	2/2, closed, monostable
Flow direction	Non-reversible
Medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas Water Neutral liquids
Medium pressure of liquid media	0.7 bar...6 bar
Medium pressure of gaseous media	0.7 bar...10 bar
Differential pressure	0.7 bar
Type of control	Pilot-controlled
Max. viscosity	22 mm ² /s
Temperature of medium	-10 °C...60 °C
Temperature of liquid media	5 °C...50 °C
Ambient temperature	-10 °C...60 °C
Flow rate Kv	27.4 m ³ /h
Standard nominal flow rate	26400 l/min
On switching time	26 ms
Response time " "on" " for liquid media	1400 ms

Feature	Value
Switching time off	20 ms
Response time " " off" " for liquid media	2000 ms
b-value	0.67
C value	82 l/sbar
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Housing material	Brass
Material number of housing	2.0402
Seals material	NBR
Armature tube material	High-alloy steel
Product weight	2570 g
CE marking (see declaration of conformity)	as per EU pressure equipment directive
UKCA marking (see declaration of conformity)	according to UK regulations for pressure equipment
Corrosion resistance class (CRC)	1 - Low corrosion stress
Max. torque for cover screw	30 Nm
Max. tightening torque for connecting thread	540 Nm
Max. tightening torque for coil fastening	2 Nm