



# Air solenoid valve VZWM-L-M22C-N38-F5-R1

Part number: 546171

FESTO



## Data sheet

Feature	Value
Structural design	Diaphragm valve servo-controlled
Actuation type	Electrical
Sealing principle	Soft
Mounting position	Preferably upright
Type of mounting	Line installation
Fitting connection	3/8 NPT
Electrical connection	Solenoid coil type MH-... , coil can be ordered as an accessory
Nominal width	13 mm
Valve function	2/2, closed, monostable
Flow direction	Non-reversible
Medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas Water Neutral liquids
Medium pressure of liquid media	0.5 bar...6 bar
Medium pressure of gaseous media	0.5 bar...10 bar
Differential pressure	0.5 bar
Type of control	Pilot-controlled
Max. viscosity	22 mm <sup>2</sup> /s
Temperature of medium	-10 °C...60 °C
Temperature of liquid media	5 °C...50 °C
Ambient temperature	-10 °C...60 °C
Flow rate Kv	2 m <sup>3</sup> /h
Standard nominal flow rate	2100 l/min
On switching time	8 ms
Response time " " on " " for liquid media	110 ms

<b>Feature</b>	<b>Value</b>
Switching time off	10 ms
Response time " " off" " for liquid media	190 ms
b-value	0.35
C value	8.8 l/sbar
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Housing material	Cast stainless steel
Material number of housing	1.4581
Seals material	NBR
Armature tube material	High-alloy steel
Product weight	400 g
Corrosion resistance class (CRC)	3 - High corrosion stress
Max. torque for cover screw	20 Nm
Max. tightening torque for connecting thread	60 Nm
Max. tightening torque for coil fastening	2 Nm