

Round cylinder DSNU-1""-8""-PPV-A

Part number: 546420

FESTO



Data sheet

Feature	Value
Stroke	8 in
Piston diameter	1 ""
Piston rod thread	3/8-24 UNF-2A
Based on norm	ISO 6432
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	Any
Piston rod end	External thread
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Variants	Piston rod at one end
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-4 °F...176 °F
Impact energy in the end positions	0,221 ft-lbf
Cushioning length	0,67 in
Theoretical force at 6 bar, retracting	55,6 lbf
Theoretical force at 6 bar, advancing	66,2 lbf
Moving mass at 0 mm stroke	2012 oz
Additional moving mass per 10 mm stroke	170 oz
Basic weight with 0 mm stroke	6747 oz
Additional weight per 10 mm stroke	312 oz
Type of mounting	With accessories
Pneumatic connection	1/8 NPT
Cover material	Wrought aluminum alloy
Seals material	NBR TPE-U(PU)

Feature	Value
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	High-alloy stainless steel