


Moment compensator FKC-25

Part number: 538715

FESTO



Data sheet

| Feature | Value |
|---|--------------------------|
| Size | 25 |
| Radial deviation +/- | 2.5 mm |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C...60 °C |
| Short-term maximum permissible load in direction of force +/- | 3000 N |
| Long-term maximum permissible load in direction of force +/- | 1400 N |
| Product weight | 119 g |
| Note on materials | RoHS-compliant |
| Articulated joint material | PA-reinforced |
| Ball stud material | High-alloy steel |
| Plate material | Wrought aluminum alloy |