

Handling module HSP-25-AE-IO-SD

Part number: 539554

FESTO

With motor unit, I/O connection and protective cover.



Data sheet

Feature	Value
Size	25
Y stroke	130 ... 170 mm
Z stroke	50 ... 70 mm
Z stroke, working stroke	25 mm
Cushioning	noise absorption through buffer Predefined braking ramp
Assembly position	Guide rail Vertically downwards
Type of gear unit	Planetary gear unit
Design structure	Cross-guide Motor unit guided motion sequence
Gear unit ratio	13,73:1
Rotor position sensor	Optical encoder
Temperature monitoring	Shutdown in case of over temperature (>70°)
Minimum cycle time	1.2 s
Repetition accuracy, intermediate positions	< 2 mm
Repetition accuracy, end positions	+/- 0,02 mm
Number of increments per revolution	500
Display resolution	128x64 Pixel
Insulation protection class	F
Max. current, digital logic outputs	60 mA
Nominal motor power	122.4 W
Nominal motor current	5.1 A
Parameters configuring interface	RS232 (9600 Baud)
Nominal voltage DC	24 V
Peak current	7.7 A
Permissible voltage fluctuation	+/- 10 %
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Protection class	IP40
Ambient temperature	0 ... 50 °C
Max. torque Mx dynamic	3.2 Nm
Max. torque Mx static	15 Nm
Max. torque My dynamic	3.2 Nm
Max. torque My static	15 Nm
Max. torque Mz dynamic	3.2 Nm
Max. torque Mz static	15 Nm
Maximum process force in Y direction	50 N
Theoretical effective power in Z direction	40 N
Product weight	10,700 g
Mounting type	with through hole With slot nuts
Materials note	Contains PWIS substances
Material information, stops	High alloy steel

Feature	Value
Material information, spring pressure piece	High alloy steel
Materials information for subbase	Wrought Aluminum alloy Anodized
Material information, holder	Wrought Aluminum alloy Anodized
Materials information for cross-guide	Heat-treatment steel
Material information, swivel lever	Case-hardened steel Burnished
Material information, slotted guide plate	Case-hardened steel Burnished
Material information, sensor rail	Wrought Aluminum alloy Anodized
Material information, ridge	Wrought Aluminum alloy Anodized
Material information, adjusting screw	High alloy steel