


# Shut off valve MS12-EE-G-V24

Part number: 541496

FESTO



## Data sheet

Feature	Value
Structural design	Piston gate valve
Actuation type	Electrical
Exhaust air function	Without flow control option
Manual override	Detenting Non-detenting
Reset method	Mechanical spring
Type of control	Pilot-controlled
Valve function	3/2, closed, monostable
Operating pressure	3 bar...16 bar
Standard nominal flow rate	25000 l/min...32000 l/min
Duty cycle	100%
Coil characteristics	24 V DC: 4.5 W
Permissible voltage fluctuations	+/- 10 %
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C...50 °C
Degree of protection	IP65
Ambient temperature	-10 °C...50 °C
Type of mounting	Optionally: Line installation With accessories
Mounting position	Any
Flow direction	Non-reversible
Product weight	3800 g
Pneumatic connection 1	Battery module
Pneumatic connection 2	Battery module
Pneumatic connection 3	G1
Pilot air supply port	Internal
Electrical connection	as per DIN EN 175301-803 Rectangular design

<b>Feature</b>	<b>Value</b>
Seals material	NBR
Housing material	Die-cast aluminum