


# Connector block CPE18-3/2-PRS-3/8-5

Part number: 550571  
Classic - do not use for new projects

FESTO

For CPE valves.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



## Data sheet

Feature	Value
Grid dimension	26 mm
Assembly position	Any
Max. number of valve positions	5
Max. no. of pressure zones	2
Burst pressure	5 MPa
Bursting pressure	50 bar
Burst pressure	725 psi
Operating pressure MPa	-0.09 ... 1 MPa
Working pressure	-0.9 ... 10 bar
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-5 ... 50 °C
Ambient temperature	-5 ... 50 °C
Max. tightening torque, valve mounting	2 Nm
Product weight	507 g
Type of mounting in-line valve manifold	with through hole
Mounting method for valve	with internal (female) thread
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 3	G3/8
Pneumatic connection, port 5	G3/8
Materials note	Conforms to RoHS
Material manifold	Wrought Aluminum alloy