

# Micro filter MS9-LFM-N3/4-AUV

Part number: 553088

FESTO



## Data sheet

| Feature                                       | Value  |
|---|--|
| Series  | MS   |
| Size  | 9  |
| Structural design                             | Fiber filter   |
| Grade of filtration                           | 0.01 µm  |
| Condensate drain                              | Fully automatic<br>Manual, non-detenting             |
| Operating pressure                            | 2 bar...12 bar                                       |
| Operating medium                              | Compressed air as per ISO 8573-1:2010 [6:8:4]        |
| Air quality class at the output               | Compressed air as per ISO 8573-1:2010 [1:7:2]        |
| Max. standard flow rate for air quality class | 6500 l/min   |
| Min. standard flow rate for air quality class | 325 l/min  |
| Filter efficiency                             | 99.9999 %  |
| Max. condensate volume                        | 225 ml   |
| Corrosion resistance class (CRC)              | 2 - Moderate corrosion stress                        |
| LABS (PWIS) conformity                        | VDMA24364-B1/B2-L                                    |
| Temperature of medium                         | 5 °C...60 °C   |
| Ambient temperature                           | 5 °C...60 °C   |
| Storage temperature                           | -10 °C...60 °C                                       |
| Residual oil content                          | 0.01 mg/m <sup>3</sup>                               |
| Type of mounting                              | Optionally:<br>Line installation<br>With accessories |
| Mounting position                             | Vertical +/- 5°                                      |
| Pneumatic connection 1                        | 3/4 NPT  |
| Pneumatic connection 2                        | 3/4 NPT  |
| Housing material                              | Die-cast aluminum                                    |
| Covering material                             | PA   |
| Compressed air filter material                | Borosilicate fiber                                   |
| Material of bowl                              | Wrought aluminum alloy                               |
| Inspection window material                    | PA   |
| Seals material                                | NBR  |
| Product weight                                | 2000 g   |