



# Rotary indexing table DHTG-140-6-A

Part number: 548089

FESTO



## Data sheet

Feature	Value
Size	140
Parallelism of plate	0.04 mm
Axial eccentricity of plate	0.02 mm
Plate concentricity	0.02 mm
Repetition accuracy of swivel angle	0.03 deg
Cushioning	Pneumatic shock absorber, hard characteristic curve, adjustable
Mounting position	Any
Mode of operation	Double-acting
Structural design	Gear coupling Gear rack/pinion Positively driven motion sequence
Position sensing	For inductive proximity sensors
Spacing	6
Operating pressure	4 bar...8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Noise level	70 dB(A)
Ambient temperature	5 °C...60 °C
Max. axial force static	4000 N
Max. pull-out torque static	300 Nm
Max. radial force static	6000 N
Max. tangential torque static	200 Nm
Theoretical torque at 6 bar	18.1 Nm
Product weight	10000 g
Type of mounting	Via through-hole and centering sleeve
Pneumatic connection	Internal thread G1/8
Plate material	Steel, galvanized

<b>Feature</b>	<b>Value</b>
Note on materials	RoHS-compliant
Stops material	Steel, galvanized
Cover material	Wrought aluminum alloy
Seals material	NBR TPE-U(PU)
Housing material	Wrought aluminum alloy