


Standard cylinder DNGZK-4"- -PPV-A

Part number: 549965

FESTO

Based on ISO 15552, NF E 49 003.1 and UNI 10 290, for proximity sensing, with trunnion mounting and adjustable end-position cushioning at both ends.

This product is only available if ordered from the Festo Corporation, USA.



Exemplary representation



Data sheet

Feature	Value
Stroke	1 ... 2,000 mm
Piston diameter	4"
Piston rod thread	UNF3/4-16
Based on the standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Piston-rod end	Male thread
Design structure	Piston Piston rod
Position detection	For proximity sensor
Variants	Single-ended piston rod
Working pressure	0.6 ... 10 bar
Mode of operation	double-acting
Operating medium	Dried compressed air, lubricated or unlubricated
Corrosion resistance classification CRC	2
Ambient temperature	-20 ... 80 °C
Cushioning length	30 mm
Theoretical force at 6 bar, return stroke	4,418 N
Theoretical force at 6 bar, advance stroke	4,712 N
Additional weight per 10 mm stroke	100 g
Basic weight for 0 mm stroke	6,210 g
Mounting type	with accessories
Pneumatic connection	NPT1/2-14
Materials information for cover	Aluminum
Materials information for seals	NBR TPE-U(PU)
Materials information, housing	Aluminum die cast
Materials information for piston rod	High alloy steel
Materials information for cylinder barrel	Wrought Aluminum alloy