

Ball screw linear actuator EGC-185- -BS-KF

Part number: 556811

FESTO



Data sheet

Feature	Value
Working stroke	50 mm...3000 mm
Size	185
Screw diameter	40 mm
Spindle pitch	40 mm/U
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Electromechanical linear axis with ball screw
Motor type	Stepper motor Servo motor
Spindle type	Ball screw
Max. acceleration	15 m/s ²
Max. speed	2 m/s
Repetition accuracy	±0.02 mm
Duty cycle	100%
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
2nd moment of area Ix	26120000 mm ⁴
2nd moment of area Iy	26120000 mm ⁴
2nd moment of area Iz	26120000 mm ⁴
Max. force Fy	15200 N
Max. force Fz	15200 N
Max. torque Mx	529 Nm
Max. radial force on actuator shaft	4000 N
Max. feed force Fx	3000 N
Torsion moment of inertia It	5140000 mm ⁴
Mass moment of inertia JH per meter of stroke	18.031 kgcm ²
Feed constant	40 mm/U
Pneumatic port on clamping unit	M5
Material of end caps	Wrought aluminum alloy Anodized

Feature	Value
Moment compensator material	Wrought aluminum alloy Anodized
Profile material	Wrought aluminum alloy Anodized
Note on materials	RoHS-compliant
Drive cover material	Wrought aluminum alloy Anodized
Slide carriage material	Steel
Guide rail material	Steel
Slide material	Wrought aluminum alloy Anodized
Spindle nut material	Steel
Spindle material	Steel