


Axial kit EAMM-A-K95-120G

Part number: 557997

FESTO



Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transferable torque	150 Nm
Product weight	2670 g
Interface code, actuator	K95
Interface code, motor in	120G
Note on materials	RoHS-compliant