


Motor flange EAMF-A-38A-60G/H

Part number: 558017

FESTO



Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C...60 °C
Product weight	154 g
Interface code, motor in	60G 60H
Interface code, coupling housing	38A
Note on materials	RoHS-compliant