


# Electric linear slide EGSK-20-25-6P

Part number: 562761

FESTO



## Data sheet

Feature	Value
Working stroke	25 mm
Size	20
Reversing backlash	20 $\mu\text{m}$
Screw diameter	6 mm
Spindle pitch	6 mm/U
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Electromechanical linear axis with ball screw drive
Homing	Reference switch
Spindle type	Ball screw drive
Max. acceleration	10 m/s <sup>2</sup>
Max. speed	0.79 m/s
Repetition accuracy	$\pm 0.01$ mm
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP10
Ambient temperature	0 °C...40 °C
Fixed bearing dynamic basic load rating	1000 N
Linear guide dynamic basic load rating	2849 N
Dynamic basic load rating, ball screw drive	860 N
2nd moment of area Iy	6100 mm <sup>4</sup>
2nd moment of area Iz	62000 mm <sup>4</sup>
Max. driving torque	0.069 Nm
Max. force Fy	764 N
Max. force Fz	764 N
Max. torque Mx	9.9 Nm
Max. torque My	3.2 Nm
Max. torque Mz	3.2 Nm
Max. feed force Fx	72 N
No-load driving torque	0.005 Nm
Ball screw drive statistical basic load rating	1450 N

<b>Feature</b>	<b>Value</b>
Linear guide statistical basic load rating	6300 N
Mass moment of inertia JH per meter of stroke	0.01 kgcm <sup>2</sup>
Mass moment of inertia JO	0.00144 kgcm <sup>2</sup>
Feed constant	6 mm/U
Statistical fixed bearing load rating	1240 N
Reference service life	3000 km
Moving mass	64 g
Slide weight	64 g
Product weight	448 g
Additional slide weight	64 g
Basic weight with 0 mm stroke	380 g
Additional weight per 10 mm stroke	27 g
Type of mounting	With internal thread and dowel pin
Material of end caps	Die-cast aluminum Coated
Profile material	High-alloy stainless steel
Note on materials	RoHS-compliant
Drive cover material	Die-cast aluminum Coated
Slide material	Steel
Spindle nut material	Steel
Spindle material	Steel